


ZL262-SG SERIES FEMALE HEADER PITCH 2.54 MM (0.100")




Specification:

- 1) To +105° Current Rate: 3 A
- 2) Dielectric Withstanding Voltage: 500 VAC
- 3) Insulation Resistance: 5000 MW
- 4) Temperature: -55°C ~ 105°C
- 5) Insulator: Thermoplastic (UL94V-0)
- 6) Contact: Copper Alloy
- 7) Contact Plated: Gold Flash

Series No.	No. of Contact (N)
ZL262-3SG	1 x 3
ZL262-4SG	1 x 4
ZL262-5SG	1 x 5
ZL262-6SG	1 x 6
ZL262-7SG	1 x 7
ZL262-8SG	1 x 8
ZL262-10SG	1 x 10
ZL262-16SG	1 x 16
ZL262-20SG	1 x 20
ZL262-40SG	1 x 40

Pitch: 2.54 mm



$$A = 2.54 * (N-1)$$

$$B = 2.54 * N$$

All dimensions in mm.