

datasheet for MLN 50/2,5 Au
 article number: 934061700



product description:	order number: 934 061-700
description:	Measuring lead, at either end 4 mm diameter plug with caged spring and 4 mm diameter socket for tower construction. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, grip and lead shatter-proof. Built in colour indicator for easy identification of insulation damages.
typ:	MLN 50/2,5 schwarz/black Au
system:	4 mm system
order number:	934 061-700
color	
other color versions:	
technical data	
pin dimensions	4 mm
type of contact:	pin (spring-loaded)
type of termination:	4 mm diameter pin and socket
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	320 x 0.10
rated voltage:	DC 60 V
rated current:	32 A
contact resistance:	6 mOhm
cable length:	50 cm
conductor size:	2,5 mm ²
cable material:	PVC
cable color:	black
material	
contact material:	contact pin: brass, contact spring: copper berylli
contact surface material:	gold- plated
housing material:	PA
environmental conditions:	
temperature range:	-15 °C to +70 °C
flammable class:	
housing:	94 V-2
cable:	94 HB
drawing	

