

up to **10MHz**
sampling rate

PPS 10

Personal Pocket Scope



Service on the move



Automotive signal testing



Industrial process checkup

World's most portable oscilloscope.

Joystick control for true hand-held operation, set all the functions only using your thumb!


Measure signals up to 2MHz with a sensitivity down to 0.1mV.

Galvanic isolated RS232 connection to your PC let you create great looking documents for later reference.


Great for hobbyist or the professional on the move!



up to **2MHz**
analog
bandwidth




PC connectivity



normal screen with large dvm



wide screen



wide screen with dvm



wide screen with large dvm

- ✓ 0.1mV sensitivity
- ✓ 200ns to 1hour/div time base in 32 steps
- ✓ Trigger mode : run, normal, once, roll, slope+/-
- ✓ DVM readout with x10 option
- ✓ dBm, dBV, DC, rms ...measurements
- ✓ Frequency readout (through markers)
- ✓ Signal storage (2 memories)
- ✓ High contrast LCD
- ✓ Supply : 5 x AAA Alkaline, Nicd or NiMH batteries (not incl.)
- ✓ joystick operation

CONTAINS

- ✓ PPS10
- ✓ user manual
- ✓ insulated safety probe
- ✓ RS 232 cable

OPTIONS

- ✓ adaptor PSU03
- ✓ HR3C 600 mAh NiMH batteries
- ✓ soft bag: BAGPS



velleman®
INSTRUMENTS

