

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200980062

Status:

Active

Overview:

PROFIBUS Solutions

Description:

PROFIBUS Straight D-Sub to Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (Straight), 24 AWG. PUR Cable, 1.0m (3.28') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Cordsets

Series

120098

Connector End A

D-Sub (9-pin)

Connector End B

Micro-Change (M12)

IP Rating

IP40, IP67

Material - Contact

Copper Alloy

Overview

PROFIBUS Solutions

Product Name

Micro-Change (M12), PROFIBUS

Protocol

EtherNet

Region

America, Asia, Europe

Type

Double Ended

UPC

78678884110

Physical

Cable Diameter

8.00mm (.315")

Cable Length

1.0m (3.28')

Color - Cable Jacket

Purple

Coupling Style

Threaded

Gender

Male-Male

Keyway

N/A

LED Indicator

No

Material - Cable Jacket

PUR

Material - Connector Body

PUR

Material - Coupling Nut

Gray Anodized Aluminum

Material - Plating Mating

Gold

Net Weight

0.124/kg

Orientation

Straight to Straight

Poles

5

Temperature Range - Operating

-20°C to +80°C

Wire Size AWG

24

Wire/Cable Type

Twisted Pair

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC/DC

Material Info

Engineering Number

BM5S60PP4M010

Reference - Drawing Numbers

Sales Drawing

SD-120098-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

120098 Series