



## Cotton Cloth Labels, Manual Marking

### • Material 270 (YE)

The bright yellow cotton labels are supplied with or without a black border in handy pocket sized booklets. For fast on-site identification of component parts, switching devices and other operating equipment.

The labels are resistant to oils, water and dust and can be removed without leaving a sticky residue. Labels can even be applied to uneven surfaces and are available in different sizes from 15 x 6mm to 38 x 11mm.

The booklet covers act as an effective barrier to dust and dirt so your labels remain clean before use.

An applicator tool is supplied with every HELASIGN booklet for clean application of the labels (e.g. with dirty hands).

For professional hand inscriptions we recommend the T82 marker pen which has fast-drying and UV-resistant ink.



Manual Marking



Always on hand: Labels in a convenient, pocket sized and lightweight booklet.

| Material Data             |                                                               |
|---------------------------|---------------------------------------------------------------|
| Material                  | <b>Type 270, Cotton cloth, yellow (YE)</b>                    |
| Operating Temperature     | <b>-40 °C to +121 °C</b>                                      |
| Curing Temperature        | <b>From +4 °C</b>                                             |
| Adhesive                  | <b>Synthetic rubber</b>                                       |
| Chem. Material Properties | <b>resistant to oils and water, removable without residue</b> |



Technical Table

| Article-No.                  | Type                   | Colour      | Width (W) | Height (H) | Quantity per/book |
|------------------------------|------------------------|-------------|-----------|------------|-------------------|
| Fabric labels without border |                        |             |           |            |                   |
| 598-12027                    | <b>TAG120B-270-YE</b>  | Yellow (YE) | 15.00     | 6.00       | 1050              |
| 598-12227                    | <b>TAG122B-270-YE</b>  | Yellow (YE) | 15.00     | 9.00       | 700               |
| 598-12427                    | <b>TAG124B-270-YE</b>  | Yellow (YE) | 19.00     | 11.00      | 440               |
| 598-12127                    | <b>TAG121B-270-YE</b>  | Yellow (YE) | 20.00     | 8.00       | 600               |
| Fabric labels with border    |                        |             |           |            |                   |
| 598-92227                    | <b>TAG122FB-270-YE</b> | Yellow (YE) | 15.00     | 9.00       | 700               |
| 598-92427                    | <b>TAG124FB-270-YE</b> | Yellow (YE) | 19.00     | 11.00      | 440               |
| 598-92127                    | <b>TAG121FB-270-YE</b> | Yellow (YE) | 20.00     | 8.00       | 600               |
| 598-92527                    | <b>TAG125FB-270-YE</b> | Yellow (YE) | 38.00     | 11.00      | 220               |
| Marker pens T82              |                        |             |           |            |                   |
| 500-50820                    | <b>T82S-BK</b>         | Black (BK)  | –         | –          |                   |
| 500-50822                    | <b>T82R-RD</b>         | Red (RD)    | –         | –          |                   |

All dimensions in mm. Subject to technical changes.

