

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0855770002

Status:

Obsolete

Overview:

[magnetic_modular_jacks](#)

Description:

Modular Jack, Right Angle, Stacked, 16 Ports

Documents:

[Drawing \(PDF\)](#)

General	
Product Family	Modular Jacks/Plugs
Series	85577
Component Type	PCB Jack
Magnetic	No
Obsolete Date	2003/09/01
Overview	magnetic_modular_jacks
Performance Category	6
Power over Ethernet (PoE)	N/A
Product Name	HyperJack™, RJ45
Physical	
Durability (mating cycles max)	500
Inverted / Top Latch	No, Yes
Lightpipes/LEDs	None
Orientation	Right Angle (Side Entry)
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Ports	16
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +80°C
Wire/Cable Type	N/A
Electrical	
Current - Maximum per Contact	1.5A
Shielded	Yes
Voltage - Maximum	125V

Material Info

EU RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

85577Series

Mates With

FCC 68 Plugs

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION