



LOC
CE
DIST
16

CAC Customer Layout Rev: D



Left Side

Connector(s): MT-RJ SECURE (No Pins)
Mode: MM
Housing Color: Yellow
Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - - - - - B
Fiber B - - - - - A


Notes:

- 1 IL tested at 1300nm.
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).

Right Side

Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Rev Per EC#		RELEASE		DATE		DIN		APVD	
A		Rev Per EC#		3/9/2009		-		QW	
P		LTR		REVISION RECORD		DATE		DIN	



Restricted To:

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters			
0	PLC	±	-
1	PLC	±	-
2	PLC	±	-
3	PLC	±	-
4	PLC	±	-

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT				
QK		Quick-Ship NetConnect		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608					
APVD		Quick-Ship NetConnect							
NAME					FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1907836	SHEET	1 of 3	REV	A

ON 2/10/20

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Qty	U of M	Description	Item No.
2	piece	Trace Label	16
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	SC Duplex Clip	13
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	2.5mm ferrule cover	11
2	piece	SC Simplex Housing, Beige	10
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	9
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNP (Plenum)	8
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ Eyed Connector Housing - Yellow	6
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	PIN KEEPER, 3.8MM	3
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	DUST COVER, MT-RJ	1

	A	Rev Per EC#	RELEASE	3/9/2009	- Q
P	LTR	REVISION RECORD		DATE	DIN AP

DIMENSIONS;
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	$\pm$	-
1 PLC	$\pm$	-
2 PLC	$\pm$	-
3 PLC	$\pm$	-
4 PLC	$\pm$	-

Restricted To:

Cable Assy Configurator		MATERIAL	HEAT TREAT	
OK	Quick-Ship NetConnect	-	-	
APVD	Quick-Ship NetConnect	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
NAME FO CIA - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO. C- 1907836	SHEET 2 of 3	REV A

D

C

B

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
BFC-ND

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

DIMENSIONS:	
meters	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK Quick-Ship NetConnect		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD Quick-Ship NetConnect				
NAME FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 1907836	3 of 3	A

D

C

B

A