


REV.	DATE	ECR NO.	DESCRIPTION
NC	11/22/08	—	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex							
8						DRAWN	G.R.S.						11/22/08		
7						CHECKED									
6						ISSUED			PART DESCRIPTION FME MALE TO TNC MALE ADAPTER						
5						SHEET	1 OF 1							PART NO. 192105	
4	CONTACT PIN	BRASS	GOLD	1	DO NOT SCALE DRAWING	CAD FILE C:/192/192105.DWG		DWG. NO.	192105.DWG	REV.	NC	SIZE	A		
3	INSULATOR	PTFE	NATURAL	1											
2	BODY	BRASS	NICKEL	1											
1	SHELL	BRASS	NICKEL	1											
	DESCRIPTION	MATERIAL	FINISH	QTY											