

① MAT'L: COPPER

PLATING: ELECTRO-TIN (.0003 MIN.)

② INSULATION: MOLDED PVC (RED)


STUD SIZES: (+.005)

02 =	.094
04 =	.119
06 =	.146
08 =	.173
10 =	.198
14 =	.265
56 =	.328
38 =	.390

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

**MWID = MAXIMUM WIRE
 INSULATION DIAMETER**
WIRE SIZE: 22-18 AWG
.25-1.5 MM²



PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"ID" MIN.			AVAILABLE STUD SIZES	STOCK THICKNESS
A-220-	.225 5.71	.157 3.99	.759 19.28	.062 1.57			02X, 04X, 06X	.028 ^{+.001/- .000} .71
A-221-	.312 7.92	.270 6.86	.946 23.26	.062 1.57			06X, 08X, 10X	.028 ^{+.001/- .000} .71
A-222-	.467 11.86	.386 9.80	1.110 28.19	.062 1.57			10X, 14X, 56X	.031 ^{+.001/- .000} .71
A-226-	.534 13.56	.552 14.02	1.309 33.25	.054 1.37			10X, 14X, 56X, 38X	.028 ^{+.001/- .000} .71
A-232-	.254 6.45	.240 6.10	.857 21.77	.062 1.57			04X, 06X, 08X	
TITLE: RING TONGUE TERMINAL INSULKRIMP 200-SERIES								
ETCmolex INCORPORATED								
DWG. NO. A CUSTOMER DWG.								
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED								
FRACTION	DEC.	ANG.	REFERENCE	SCALE: NTS	DATE			
±	±	±		DRWN. BY: K-	10-23-84			
				CHKD. BY: GZ	11-9-84			
				APPRD. BY:				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19054-0044](#)