



Description: CAT6 molded & booted patch cable

Part No: 73-889X-XXX

Application: Patch cable

Crimp Tool: N/A

Impedance: N/A

Frequency Range: N/A

Material: Plug RJ-45, Gold plated on contacts

Hood PVC

Cable UTP, 24 AWG, 4 twisted pairs with PE
divider, stranded bare copper, UL ETL
EIA/TIA-568A verified category 6

RoHS Compliance: Yes

Technical Detail: N/A

DRAWING NO.
73-889X-XXX-CUST

REVISIONS

01 OFFICIAL RELEASE

06-11-10 J J T H

02 CHANGE VIEW



03-29-11 J J D

ECO-11-0058

受控 CONTROLLED DOCUMENT				
编号 P/N	73-889X-XXX-CUST	版本 Rev	02	日期 Rel'd Date Jul11,11

TABLE 1

X=COLOR	PART NUMBER	LENGTH (FEET)	DESCRIPTION
0-GRAY	73-889X-1	1	CAT6 MOLDED & BOOTED PATCH CABLE, 1FT
1-BLACK	73-889X-3	3	CAT6 MOLDED & BOOTED PATCH CABLE, 3FT
2-BLUE	73-889X-5	5	CAT6 MOLDED & BOOTED PATCH CABLE, 5FT
3-GREEN	73-889X-7	7	CAT6 MOLDED & BOOTED PATCH CABLE, 7FT
4-RED	73-889X-10	10	CAT6 MOLDED & BOOTED PATCH CABLE, 10FT
5-YELLOW	73-889X-14	14	CAT6 MOLDED & BOOTED PATCH CABLE, 14FT
6-WHITE	73-889X-25	25	CAT6 MOLDED & BOOTED PATCH CABLE, 25FT
7-ORANGE	73-889X-50	50	CAT6 MOLDED & BOOTED PATCH CABLE, 50FT
8-PINK	73-889X-100	100	CAT6 MOLDED & BOOTED PATCH CABLE, 100FT
9-PURPLE			



PIN ASSIGNMENT	
	RJ-45 PLUG
WHITE/ORANGE	1 RJ-45 PLUG
ORANGE	2
WHITE/GREEN	3
GREEN	6
BLUE	4
WHITE/BLUE	5
WHITE/BROWN	7
BROWN	8

DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	JEAN.JIN	03-29-11
X	± 0.5	CHECKED BY	DATE
		JEAN.JIN	03-29-11
X.X	± 0.3	APPROVED BY	DATE
X.XX	± 0.15	DONALD	03-29-11
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.



TITLE
CAT6 MOLDED & BOOTED PATCH CABLE

SHEET 1 OF 1 DRAWING NO. 73-889X-XXX-CUST SIZE A

SONNENFELD RESELLER COMPANY