


3.0X1.0mm(1104) RIGHT ANGLE BI-COLOR SMD CHIP LED



UNIT : MM[INCH]

TOLERANCE : $\pm 0.2[\pm 0.0079]$ UNLESS OTHERWISE NOTED

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	
APBA3010MGSYW01	MEGA BRIGHT GREEN(InGaAlP)	WHITE DIFFUSED	40	60	140°
	SUPER BRIGHT YELLOW(InGaAlP)		50	100	

APPROVED:

J.Lu

CHECKED:

J.Chao

DRAWN :

L.N. Sheu

SCALE :

10 : 1

DATA NO. : F9436

V.1

DATE : OCT/30/2000