


LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	18 DAY
				C		REV & REDRAWN PER 0720-0040-93	3-17-93		

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed	
16-14HD AWG SOLID OR STRANDED		16-14HD AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
16-14HD AWG SOLID OR STRANDED		NOT APPLICABLE	

△ STAMP AMP 16-14HD* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
1.04-2.62mm² [2.050-5.180] CIR MILS
SOLID OR STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLG DEC ±
3 PLG DEC ±
ANGLES

DR 3-17-93
TA BRINKMAN
CHK 3-17-93
DA PATTERSON
APPD 3-17-93
DE MILLER
APPD 3-17-93
UL MECKLEY
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING TONGUE,
HEAVY DUTY, SOLISTRAND™

FINISH
TIN PLATE
0.00254L [0.00100] MIN
THK PER MIL-T-10727

NAME
AMP
AMP Incorporated
Harrisburg, PA 17105-3608

SIZE
CAGE CODE
00779
DRAWING NO
C=320759

SCALE
4:1
SHEET
1 OF 1