

Video and Audio Cables and Connectors

These quality cables and connectors
are perfect for your video and
audio installations.





F59-Type Video Plug, COUPLER, AND ADAPTER

The **F59-Type Video Plug** is solderless and plated with 24-karat gold. It's for use with RG-59/U cable.

Installation requires only a sharp knife or wire stripper and a suitable crimping tool.

The **Video Coupler** is also 24-karat gold-plated, and you can couple cables terminated with male F-type plugs for extended runs with the female-to-female adapter.

The **Video Adapter** features an F-type jack and a Quick-Connect type plug to adapt male F-type cable ends to Quick-Connect plugs. Use it with dual-shielded RG-6 coax cable.

Video Connectors, BALUNS, AND SPLITTERS

The **Twist-On RG-6 Cable/Satellite TV Coax Connectors** don't require any tools or crimping! The "F" connectors twist on easily and securely. Use them with dual-shielded RG-6 coax cable.

The **TV Signal Amplifier** provides superior picture stability and clarity. It gives you an additional 10 decibels of signal on an output port and handles signals up to 900 MHz.

The **Signal Combiner** combines VHF and UHF signals into one 75-ohm signal for input to a TV or VCR. Use it in reverse as a splitter. Plus, it's ideal for 300-ohm VHF and UHF connections and features a Quick-Connect plug for fast connections.

The **Right-Angle Slip-On Video Balun** connects a matching transformer with a 300-ohm twin-lead antenna system and a TV set and VCR that has a 75-ohm antenna input.

The **Video Balun** connects a VCR's VHF output to a TV's 300-ohm VHF input. Use the matching transformer to connect a 75-ohm antenna system to a TV/VCR via the 300-ohm antenna input. Connect the balun directly to an indoor 300-ohm antenna's terminals.

The **Cable/Satellite TV Signal Splitters** handle signals up to 2 GHz for broadband and satellite applications. The FA863 has five female threaded "F" connectors; the FA865 has three.

The splitters optionally can be mounted to the wall. A 75-ohm termination cap is included.

The **75-Ohm Hybrid (UHF/VHF) Splitters** divide one incoming 75-ohm signal into two or three with only 5.5-dB loss. The splitters have 24-karat gold-plated connectors for better connections.

Stereo Connection Cable


A **Stereo Connection Cable** carries one stereo channel of audio signal between an amplifier or a receiver and a stereo component.

It has fully shielded copper stranding, which keeps interference at a minimum. Two 24-karat gold-plated RCA plugs have molded strain reliefs that protect the cable against bends and breaks.

Item	Code
Crimp-On F59-Type Video Plugs, 2-Pack	FA854
Video Coupler, F-Connector, Female/Female	FA855
Twist-On RG-6 Video Adapter/Slip-On Connector	FA857A

Item	Code
Video Connectors, Baluns, and Splitters	
Twist-On RG-6 Cable/Satellite TV Coax Connectors	
10-Pack	FA866
TV Signal Amplifier (10-dB)	FA864
Signal Combiner	FA858A
Right-Angle Slip-On Video Balun	FA856
Video Balun	FA859A
Cable/Satellite TV Signal Splitters, 2-GHz	
1-4	FA863
1-2	FA865
75-Ohm Hybrid (UHF/VHF) Splitters	
2-Pack	FA860A-R2
3-Pack	FA861A-R2

Item	Code
Stereo Connection Cable	
12-ft. (3.6-m)	EJ100-0012



Shielded Y Cord

The **Shielded Y Cord** splits a single audio signal into two signals or combines two audio signals into one. One model has one male RCA plug and two female RCA jacks; another model has the opposite. All have molded strain reliefs and come in 4-inch (10.2-cm) lengths. A third model has one 3.5-mm mini plug and two female RCA jacks.

Speaker Wire & Mini Stereo Headphone Extensions

Speaker Wire features 18-gauge, zip-cord style construction. The conductors are parallel. Use the cable to connect your speakers to your stereo components.

The coiled and non-coiled versions of the **Mini Stereo Headphone Extension Cords** provide up to 10 feet (3 m) of distance from your stereo equipment. They have a 3.5-mm, right-angle stereo plug on one end and a 3.5-mm stereo jack on the other. Both ends have molded strain reliefs.

SCREW-ON RG-59 PLUGS

Screw-On RG-59 Plugs are 24-karat gold-plated F-type plugs with molded strain relief at each end. They are fully shielded and can carry a 75-ohm signal between one piece of video equipment and another.

Item	Code
Shielded Y Cord, 4-in. (10.2-cm)	
RCA Plug Male/(2) RCA Jacks, Female/Female	EJ400
RCA Jack Female/(2) RCA Plugs, Male/Male	EJ401
3.5-mm Mini Plug/(2) RCA Jacks, Female/Female	EJ402

Item	Code
Speaker Wire, Parallel Conductors	
25-ft. (7.6-m)	EJ505-0025
50-ft. (15.2-m)	EJ505-0050
100-ft. (30.4-m)	EJ505-0100
Mini Stereo Headphone Extension Cords	
Coiled	
10-ft. (3-m)	EJ501
Non-Coiled	
10-ft. (3-m)	EJ502

Item	Code
Screw-On RG-59 Plugs	
3-ft. (0.9-m)	EJ203-0003
6-ft. (1.8-m)	EJ203-0006
12-ft. (3.6-m)	EJ203-0012
25-ft. (7.6-m)	EJ203-0025



EHN058



FA871



FA876



FA878

S-Video Cable & S-Video coupler

S-Video Cable terminates with right-angle 4-pin-mini DIN connectors. Use the cable to provide a video link between your DVD player, video camera, or VCR, and your TV or monitor.

Rated at 75 ohms, the cable is made of 85% tinned copper braid and foil and features molded hood assemblies.

The **S-Video Coupler** features a pair of 4-pin-mini DIN female connectors that make connecting two S-video cables quick and easy. Use it to extend your video hookups.

Audio/Video ADAPTERs, Couplers, and CONVERTERs

Deluxe Audio and Video Couplers/Adapters minimize signal degradation from your high-end video, audio/video, and audio/stereo equipment. The FA870 links CATV, CCTV, and video cards. The FA871 joins two RCA male cables. The FA872 converts digital signals. The FA879 joins an RCA connector to a BNC connector.

Banana Plugs feature gold-plated contacts and assemblies for solid, reliable, and high-quality speaker connections. The two-piece assembly uses two screws to hold the cable core and jacket to the plug. And, you can use them with our Binding Posts (FA875).

Binding Posts also have gold-plated contacts for solid, reliable, and high-quality speaker connections. They snap securely into any of our GigaStation, GigaStation+, or GigaStation2 Wallplates. Plus, the binding posts are color coded for easy identification and installation. They accept Banana Plugs (FA873), spade lugs, or bare wire.

RCA Jacks support RCA plugs in the front and rear. Use them with any RCA audio cable and any of our GigaStation, GigaStation+, or GigaStation2 Wallplates.

Audio Adapters convert RCA or 3.5-mm connectors to 1/4" connectors.

Item	Code
S-Video Cable	
6-ft. (1.8-m)	EHN058-0006
12-ft. (3.6-m)	EHN058-0012
25-ft. (7.6-m)	EHN058-0025
50-ft. (15.2-m)	EHN058-0050
100-ft. (30.4-m)	EHN058-0100
S-Video Coupler	
4-Pin Mini DIN, Female/Female	FA315

Item	Code
Deluxe Audio and Video Couplers/Adapters	
RCA Female/BNC Male Video Adapter	FA870
RCA Female/RCA Female Audio/Video Coupler	FA871
RCA Female/3.5-mm Mono Audio Adapter	FA872
RCA Female/BNC Female Coupler	FA879
Banana Plugs	
2-Pack	FA873
Binding Posts	
2-Pack	FA875
RCA Jacks	
2-Pack	FA874
Audio Adapters	
RCA Female/1/4" Male, Mono	FA876
3.5-mm Male/1/4" Female, Mono	FA877
3.5-mm Female/1/4" Male, Stereo	FA878