

APC Workshop SurgeArrest 7 Outlets

Part Number: PDIY7



Output

Number of Outlets	7
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15A
Cord Length	2.44 meters



Surge Protection and Filtering

Surge energy rating	800 Joules
eP Joule Rating	820
EMI/RFI Noise rejection (100 kHz to 10 mHz)	20 dB
Peak Current Normal Mode	6 kAmps
Peak Current Common Mode	12 kAmps
Let Through Voltage Rating	< 330

Physical

Net Weight	0.72 KG
Maximum Height	380.00 mm
Maximum Width	70.00 mm
Maximum Depth	45.00 mm
Shipping Weight	0.50 KG
Shipping Height	380.00 mm
Shipping Width	109.00 mm
Shipping Depth	51.00 mm
Master Carton Units	12.00
Master Carton Dimensions (Length x Width x Height)	789 x 324 x 144 mm
Master Carton Weight	10.10 KG
SCC Codes	1073130423832 1
Color	Yellow
Units per Pallet	180.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters

Conformance

Regulatory Approvals	CSA,UL 1449
Standard Warranty	3 years repair or replace
UL 1449 TVSS Rating	330V