

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

14


R

REV PER 0G3A-0279-03

02SEP03

JR

MS



1 SEE TABLE FOR STAMPING

2 WIRE INSUL. DIA 3.18-5.84 [.150-.230]

3 TONGUE MATL THK, 1.02±0.05 [.040±.002]

4 MATERIAL: BODY - SEE TABLE
SLEEVE - NI SIL PER ASTM B1225 MAX RECOMMENDED OPERATING TEMP
649°C [1200°F]6 CIRCULAR MIL AREA 2.62mm²-6.64mm²
[5180-13100] STARND WIRE

OBSOLETE	AMP 12 10CH	CHROMEL	GRAY	500	LOOSE PIECE	2-323749-1
	AMP 12-10	NICKEL PER ASTM B162	ORANGE	500	LOOSE PIECE	323749
	STAMPING	BODY MATERIAL	SLV COLOR	QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN L OLMEDA

100CT94

CHK M ELLIS

100CT94

APVD S BORTNER

100CT94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA 17105NAME
TERMINAL, RING TONGUE,
STRATO-THERM, DIAMOND GRIP,
WIRE SIZE: 12-10 AWGSIZE CAGE CODE DRAWING NO RESTRICTED TO
A3 00779 C-323749

SCALE 4:1 SHEET 1 OF 1 REV R