





# MATERIALS

1. HOUSING : P.B.T. (UL 94V-0), BLACK.
2. TERMINAL : S.Q. 0.64mm GOLD PLATING.

# SPECIFICATION

1. CURRENT RATING : 3 AMP. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE : 1000V AC R.M.S. FOR ONE MINUTE.
3. INSULATION RESISTANCE : 5000M OHMS MIN. AT 1000V DC.
4. OPERATING TEMPERATURE : -55°C TO +105°C.

## Dimensions

| Pos. | A     | B     | C     |
|------|-------|-------|-------|
| 10   | 32.00 | 27.94 | 10.16 |
| 14   | 37.08 | 33.02 | 15.24 |
| 16   | 39.62 | 35.56 | 17.78 |
| 20   | 44.70 | 40.64 | 22.86 |
| 24   | 49.78 | 45.72 | 27.94 |
| 26   | 52.32 | 48.26 | 30.48 |
| 30   | 57.40 | 53.34 | 35.56 |
| 34   | 62.48 | 58.42 | 40.64 |
| 40   | 70.10 | 66.04 | 48.26 |
| 50   | 82.80 | 78.74 | 60.96 |

玄茂科技股份有限公司  
HSUAN MAO TECHNOLOGY CO., LTD.

制表日: 2006/01/10

DRAWING.

Jolin

APPROVED

UNIT

MM

APPD.

CKD.

SCALE

TOLERANCE

PART NAME

2.54x2.54mm FULLY SHROUDED  
HEADER 180° LONG LATCH

PART NO.

C3000-XXSLXB00R

REV.

A