




1.CABLE: NO UL, 28AWG(7/0.127), TINNED AND STRANDED COPPER WIRE
INSULATOR: PVC, ID: 0.85mm, CABLING: 9C+DRAIN WIRE
SHIELD: AL/MY COVERAGE

JACKET: PVC, COMPLIANCE ROHS, COLOR: BEIGE, O.D: 5mm

2. 1PCS CONNECTOR: D-SUB 25 WAYS MALE SOLDER TYPE CONNECTOR

INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE

CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED

SHELL: NICKEL PLATED,

CONNECTOR COMPLIANCE ROHS

3. 1PCS CONNECTOR: D-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR

INSULATOR: P.B.T.+GLASS FIBER, COLOR: BLUE

CONTACT: COPPER ALLOY, GOLD FLASH OVER NICKEL PLATED

SHELL: NICKEL PLATED,

CONNECTOR COMPLIANCE ROHS

4. HOOD: PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER

ON INNER MOLD AND INJECTION OUTER MOLD WITH

THUMB SCREW #4-40 & #4-48 UNC

COLOR: BEIGE, COMPLIANCE ROHS

5 Fulfill ROHS Guideline

6. ELECTRONIC TEST: 100% OPEN SHORT+MISS WIRE TEST

PIN OUT

DB9PIN FEMALE(J1)	WIRE	DB25PIN PLUG(P1)
1	---	8
2	---	3
3	---	2
4	---	20
5	---	7
6	---	6
7	---	4
8	---	5
9	---	22
SHELL	DRAIN WIRE	SHELL

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: DB9 PIN FEMALE TO DB25 PIN MALE BEIGE COLOR			SCALE N.T.S
			SIZE A4
			UNIT
DWN NO D-1051-XX			CHECKED BY & DATE
			APPROVED BY & DATE