


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/31/10	D.GRIFFIN
B	ECN 6271: UPDATED HOODS TO NEW LOGO	7/9/12	D. DESJARDIN



MODEL NUMBER	LENGTH FT [METERS]
CSMUZ15MF-1	1.0 [.31]
CSMUZ15MF-2.5	2.5 [.76]
CSMUZ15MF-5	5.0 [1.52]
CSMUZ15MF-10	10.0 [3.05]
CSMUZ15MF-15	15.0 [4.57]
CSMUZ15MF-25	25.0 [7.62]
CSMUZ15MF-50	50.0 [15.24]
CSMUZ15MF-125	125.0 [38.10]

WIRE TABLE		
"P1"	"J1"	COLOR
1	1	BLACK
2	2	RED
3	3	WHITE
4	4	GREEN
5	5	ORANGE
6	6	BLUE
7	7	WHITE/BLACK
8	8	RED/BLACK
9	9	GREEN/BLACK
10	10	ORANGE/BLACK
11	11	BLUE/BLACK
12	12	BLACK/WHITE
13	13	RED/WHITE
14	14	GREEN/WHITE
15	15	BLUE/WHITE
SHELL	SHELL	DRAIN

NOTES:

1. DRAIN WIRE TIED TO CONNECTOR SHELLS.
2. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.
4. DUST COVERS INSTALLED FOR SHIPPING. (NOT SHOWN)

RoHS Compliant

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = 0.2 .XX = 0.02 .XXX = 0.005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D.FRISIELLO	4/7/10		
	CHECKED BY F.MAO	4/7/10	CATEGORY DATA CABLING	
	APPROVED BY S.SMITH	4/7/10	PRODUCT DESCRIPTION LOW SMOKE ZERO HALOGEN DATA CABLE	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
	COLOR VARIATIONS MAY OCCUR		DWG. NO. CSMUZ15MF	REV. B
	SCALE: NONE		CAD FILE: CSMUZ15MF.SLDDRW	SHEET 1 OF 1