

EK EKJB 130 T



Sample photo

Order symbol: EKJB 130 T
Product nbr: 2538113
Description: Enclosure, PC
Remarks: Transparent cover

EAN:	6418074013750
El. number:	
Finland:	3425456
Italy:	7502020
Sweden:	2538113
Norway:	

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	280	190	130
inch:	11.0	7.5	5.1

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	Clear transparent
Cover screws material:	Polyamide
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Short term:	-40 ... 120 °C
Continuous:	-40 ... 80 °C
Short term:	-40 ... 250 °F
Continuous:	-40 ... 175 °F

Accessories:

EKJB	Base, PC
EKJ 30-G	Cover
EKJ 80-G	Cover
EKJ 30-T	Cover
EKJ 80-T	Cover
EKJVT	Mounting plate
EKJXT	Mounting plate Pertinax
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKZR	Extension frame

Rating:

Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 62262): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Certificates:

Germanischer Lloyd (GL)
Underwriters Laboratories
Det Norske Veritas
Bureau Veritas
Fimko
Lloyds Register of Shipping (LR)
Europe EN 62208: 2003
UL Canada
Gost R

EK 280x190x130-180

