

**NYS2202****NYS Product Range / Jacks****TECHNICAL DATA****Electrical**

Rated Current: Depends on mating connector

Contact Resistance: Depends on mating connector

Insulation Resistance: &gt; 1 G Ohm

Dielectric strength: 500 dc

**Mechanical**

Life Cycles: 5000

Cable OD: 4-9 mm

Solderability: IEC68-2-20

Operating Temperature: -25° C to +70° C

**Material**

Housing/Handle: Brass Ni/Au/black plated or Zinc Diecast

Insulation: Thermoplastic

Contacts: Brass Ni/Au plated

Strain Relief: CRIMP type SnCe plated

**Copyright © 2005****Neutrik® AG.****All Rights Reserved.****NEUTRIK®**

CONNECTING THE WORLD

**Neutrik® AG - Headquarters**

Im alten Riet 143

9494 Schaan

Principality of Liechtenstein

**phone:** +423 2372424**fax:** +423 2325393**email:** [neutrik@neutrik.com](mailto:neutrik@neutrik.com)**net:** <http://www.neutrik.com>