

MZB 1,5-F

Order No.: 3003761



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3003761>

Feed-through modular terminal block, Type of connection: Spring-cage connection, Cross section: 0.14 mm² - 2.5 mm², AWG 26 - 14, Width: 11 mm, Height: 22 mm, Color: gray

Commercial data

GTIN (EAN)	 4 017918 107031
sales group	A611
Pack	50 pcs.
Customs tariff	85369010
Catalog page information	Page 168 (CL-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Number of levels	1
Color	gray
Insulating material	PA
Inflammability class acc. to UL 94	V0

Dimensions

Width	11 mm
Length	32 mm
Height	22 mm

Technical data

Maximum load current	24 A (with 2.5 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	17.5 A
Nominal voltage U _N	800 V

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Type of connection	Spring-cage connection
Stripping length	9 mm
Internal cylindrical gage	A1

Certificates / Approvals



Certification

CUL, GOST, PRS, UL

Certification Ex:

KEMA-EX

Accessories

Item	Designation	Description
Assembly		
3024180	D-MZB 1,5-F	End cover, Width: 4 mm, Color: gray
3024449	D-MZB 1,5-F BU	End cover, Width: 4 mm, Color: blue
Marking		
0803647	ZBFM 5:SO/CMS	Special printing, Zack marker sheet, flat, 120-section, divisible, marking according to customer requirements
Tools		
1204517	SZF 1-0,6X3,5	Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip
3024287	ZFK-BW 2-5	Actuation tool, for loosening the tension spring, 2-pos.

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;