





NOTE

- 1 - 8-32 UNC X (.219) BINDER HEAD, COMBINATION , TERMINAL SCREWS
AND CUPWASHERS
- 2- **BUTTON LEVER BRACKET ASSEMBLY MAY BE SET IN ANY POSITION
AROUND AXIS OF PLUNGER**

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION 
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE - - - - - 2 LBS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE - - - - - 1/2 LB MIN	L23 20A 125, <u>250</u> OR 480 VAC 10A 125 VAC "L" 1HP 125 VAC, 2HP <u>250</u> VAC 1/2A 125 VDC, 1/4A 250 VDC	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
BASIC SWITCH REPLACEMENT - - - BA-2R708-P7		WEIGHT .670 LB