

NOTES: UNLESS OTHERWISE SPECIFIED


1. CONSTRUCTION:

INSULATOR: P.V.C. AVAILABLE IN BLACK OR RED.
CONTACT: ANACONDA 7021 OR BOILCAT C97.
GOLD PLATED.
SOCKET: BRASS. TIN PLATED.

2. PERFORMANCE:

MAXIMUM CURRENT: 7.5 AMPS
MAXIMUM VOLTAGE: 300 V
MAXIMUM TEMPERATURE: 122°F (50°C)

REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .XXX ± ±		CONTRACT NO.		DESCRIPTION	
MATERIAL SEE NOTE.		APPROVALS		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
FINISH SEE NOTE.		DRAWN		SIZE CODE IDENT NO. DRAWING NO.	
USED ON		APPROVED BY		A 08505 9339	
APPLICATION		DO NOT SCALE DRAWING		SCALE 2:1	
				SHEET 1 OF 1	