

平面ハンドル FLUSH HANDLES

問題点を改良 次世代平面ハンドル



A-1750-1-1R



A-1750-3-1R



キーNo.0200
Key



A-1750
ステンレス製

特 徴 Feature

PAT.PEND.

- 扉を開めるだけのワンタッチロック
- 新機構で止め金かじりの問題点を改良
- ステンレス製で耐食性に優れています。
- 右開き用・左開き用(本図・写真共右開き用です。)
- One-touch locking only by closing the door.
- New mechanism is incorporated in the stopper plate for improvement.
- Corrosion-resistant stainless steel is used.
- The left-hand or right-hand use. (Drawings and photo show the right-hand use.)

- 仕 様 ●材 質 : 冷間圧延ステンレス鋼板(SUS304)
●表面仕上 : ヘアライン仕上
●鍵 番 号 : 0200
●付 属 品 : ビスセット・キー2本付属
●適用板厚 : 0~3.2mm

- 用 途 ●配分電盤・制御盤
納 期 ●標準在庫品
備 考 ●ラッチのカバーを外してからラッチをハンドルに取付けてください。(A-1750-2~4)
●永くご使用頂くために定期的に摺動部に高性能潤滑剤C-985(1367ページ)を塗布してください。
●本製品の錠前はキー先端部での操作となります。
●鍵を必要以上に回転させると錠前部・鍵先端部が破損する恐れがありますのでご注意ください。

- Speci- ●Material: Cold rolled stainless steel (SUS304)
fications ●Finish: Hairline finish
●Key No.: 0200

- Accessories: Screws and two keys
●Applicable panel thickness: 0~3.2mm

- Specific use ●Power/distribution and control boards
Remarks ●Remove the latch cover before fitting the latch on the handle.

- To prolong the life of the product, apply a regular coating of high-performance lubricant C-985 (P.1367) to the sliding parts.
●The lock on this product is operated with the tip of the key.
●Note that care is required, since turning the key more than is necessary risks damaging the lock or the tip of the key.

