



Power Distribution Blocks

T&B Catalog Number:

PDS3610

UPC Number:

78378647376

Status:

Active

Description:

Three Hole Terminal Block, Color: Gray, 1 Wire: Cu / Al 1/0 - #6 Awg, 2 Wires: Cu Only #6 Awg, 3 Wires: Cu Only #8 Awg, Voltage Rating: 600 Volts Max, Terminal Block Supplied

Features

Insulated housing provides fast, clean, safe installation and controlled dielectric strength. Easily installed and position-locked with DIN rail or screw mounting.

Grooved contact surfaces penetrate conductor oxides for best contact.

General

Style	Terminal Block
Color	Gray
Mounting Method	Top Hat rail
Wire Range	1/0 - 6 AWG
Screw Size	5mm
Maximum Current	150A CU/120A AL
Tightening Torque	90 lb.-in.

Dimension Information

Width (inches)	1.9
Height (inches)	1.9
Depth (inches)	1.7

Specifications

Temperature Rating	80°C Max
Voltage Rating	600 Volts Max.
Flamability Rating	UL 94 V-2

Packaging

T&B Order Multiple	2
T&B Inner Pack	2
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	170 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000213
Overview	Available on Website
Conductor Table	Available on Website

Notes

Terminal blocks supplied with Oxide Inhibiting Compound.

Certifications



File Nbr:
E66436

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com