




THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.

REV.	BY	DATE	APPRVL.	P/N
C	DMS	3/23/98	BT	DC27
ADDED SHAFT CHART				

SPECIFICATIONS

ACCURACY ----- $\pm 0.35\%$ OF VOLTAGE RATIO
REPEATABILITY ----- $\pm 0.02\%$ RESOLUTION OF POT
OPERATING TEMPERATURE RANGE ----- -30°C TO 85°C
TURNS ----- 10 (000 TO 999 COUNTS)
LOCK ----- OVER THE CENTER
HOUSING MATERIAL ----- HIGH TEMP. BLACK PLASTIC

PANEL LAYOUT




NOTES

1. COMPATIBLE ETI SYSTEMS POTENTIOMETERS 3 TO 30 TURNS.
MW20B MW46B MH20B
MW22B MR46B MH46B
2. POT/DIAL COMBINATIONS AVAILABLE
SEE ETI SPECIFICATION DC22.
3. OTHER SHAFT SIZE BUSHINGS AVAILABLE
4. NUMBERS INCREASE WITH CLOCKWISE ROTATION

PART #	SHAFT DIA.	LOCKING UNIT
DC27L-1/4	0.250	YES
DC27N-1/4	0.250	NO
DC27L-1/8	0.125	YES
DC27N-1/8	0.125	NO
DC27L-6mm	6mm	YES
DC27N-6mm	6mm	NO
DC27L-3mm	3mm	YES
DC27N-3mm	3mm	NO

TOLERANCES			
XX = $\pm .010^{\circ}$	FRACT. = $\pm .1/64^{\circ}$	DATE: 3/18/98	SCALE
XXX = $\pm .005^{\circ}$	ANGLES = $\pm .1/2^{\circ}$	BY	DMS
ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.			
CODE IDENT: 19477			



TURNS COUNTING DIAL

PART NO. DC27