



BNC Connectors, 75 Ohm (Continued)

Press Fit Vertical Metalized PC Board Mount Jacks (Continued)




PC Board Thickness
.093 [2.36] Min.
Part No. 221336-3
PC Board Thickness
.125 [3.17] Min.
Part No. 221336-4




Recommended PC Board Layout

Right-Angle PC Board Panel Mount Jack



Part No. 415373-1



Maximum Panel Thickness .250 [6.35]
Recommended Panel Cutout



Right-Angle PC Board Mount Jack



Maximum PC Board Thickness .100 [2.54]

Recommended PC Board Layout


Body Plating	Dielectric	Contact Plating	Center Contact Dimension	Length	Part Number
Nickel	TPX	Gold2	.171	4.34	413558-1
Tin-Lead	TEFLON	Gold2	.171	4.34	413558-2
Nickel	TPX	Gold2	.131	3.33	413558-3
Tin-Lead	TPX	Gold1	.171	4.34	413558-4
Nickel	TPX	Gold1	.171	4.34	413558-5

Gold1 — .000030 [0.00076] thick
Gold2 — .000050 [0.00127] thick


Bulkhead Jack Adapter

Plating

Body — Nickel
Center Contact — Gold
Dielectric — Polymethylpentene



Part No. 222117-1




Maximum Panel Thickness .250 [6.35]
Recommended Panel Cutout

Right-Angle Adapter (Jack-Plug)

Plating

Body — Nickel
Center Contact — Gold
Dielectric — Polymethylpentene



Part No. 415020-1