



Sample photo

Order symbol: P 404012
Product nbr: 7094450
Description: Enclosure
Remarks: Polyester

EAN: 6418074004444
El. number:
 Finland 3423681
 Denmark 8212005714
 Italy 7331065
 Sweden 2536239

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:		L	W	H	Rating:
mm:		401	406	120	Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes UV resistance: UL 508 Flammability Rating (UL 746 C 5): UL 94 5V Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 12, 13
inch:		15.8	16	4.7	
Materials:					
Material:		GRP			Certificates:
Base colour:		RAL 7001			
Cover colour:		RAL 7001			
Cover screws material:		Stainless steel			
Gasket material:		EPDM			
Temperatures:					
Short term:		-50 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-60 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
PM 4040		Mounting plate			
ARH 40		DIN-35 Mounting rail			
MRS 28541		Wall fastening lug set			
PH A & AH A/B		Hinge set			

