





- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER. COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR-BRONZE.
- 3 CONTACT FINISH:
 - UNDERPLATE (ENTIRE CONTACT) – 0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
 - ON MATING SURFACES– CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT
 - ON LEADS– 0.00381 MIN TIN PER ASTM B 545, OVER UNDERPLATE
 - LUBRICATION (MIN MATING SURFACES): SURFACE CONDITIONER AFTER PLATING.
- 4 PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- 5 CUSTOMIZED PART, HOUSING MOLDED WITHOUT END GUIDE LUGS.
- 6 OBSOLETE PART NUMBER.
- 7 CONTACT FINISH:
 - UNDERPLATE (ENTIRE CONTACT) – 0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
 - ON MATING SURFACES– CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT
 - ON LEADS– FLASH GOLD PER ASTM B 488, OVER UNDERPLATE
 - LUBRICATION (MIN MATING SURFACES): SURFACE CONDITIONER AFTER PLATING.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



TYPICAL COLD HOLD FOR ALL ASSEMBLIES

	NO	70	35	71.88	7	144	2-5536510-8
	NO	94	47	95.88	7	192	2-5536510-7
	NO	46	23	47.88	7	96	2-5536510-6
	NO	22	11	23.88	7	48	2-5536510-5
OBSOLETE	YES	94	47	95.88	3	192	2-5536510-4
	YES	46	23	47.88	3	96	2-5536510-3
	NO	34	17	35.88	3	72	1-5536510-5
	NO	22	11	23.88	3	48	1-5536510-4
	NO	94	47	95.88	3	192	1-5536510-3
	NO	106	53	107.88	3	216	1-5536510-2
	NO	70	35	71.88	3	144	1-5536510-1
OBSOLETE	NO	130	65	131.88	3	264	1-5536510-0
	NO	106	53	107.88	3	216	5536510-9
	NO	118	59	119.88	3	240	5536510-8
OBSOLETE	NO	82	41	83.88	3	168	5536510-7
	NO	58	29	59.88	3	120	5536510-6
	NO	70	35	71.88	3	144	5536510-5
	NO	94	47	95.88	3	192	5536510-4
	NO	46	23	47.88	3	96	5536510-3
	NO	22	11	23.88	3	48	5536510-2
	YES	10	5	11.88	3	24	5536510-1
POSITIONING PEGS	C	B	A	FINISH	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 31AUG04	TE Connectivity	
DIMENSIONS: mm		CHK R. WERTZ 31AUG04	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D R. WERTZ 31AUG04	PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		
1 PLC ± -		SIZE		
2 PLC ± -		CAGE CODE		
3 PLC ± -		DRAWING NO		
4 PLC ± -		RESTRICTED TO		
ANGLES		WEIGHT		
FINISH		A1 00779 5536510		
MATERIAL		CUSTOMER DRAWING		