


## Electrical Specs.

Ind.  $445\mu\text{H} \pm 5\%$  @ 1.0MHz.  
 Q 44 Min. @ 1.0MHz  
 SRF 5MHz. Min.  
 DCR  $2.20\Omega$  Max.



### Notes:

- Operating temperature:  $-55^\circ\text{C}$  to  $+105^\circ\text{C}$
- RoHS Compliant

NEXT ASSEM	USED ON	LTR.	REVISION		BY	DATE
Part #:		28M443J-1LF				
DRAWN BY	KB	APPROVED BY	KB	ENG	QA	MFG

Unless otherwise specified  
dimensions are in inches.  
in. (mm)

This drawing or  
specification is the  
property of Gowanda  
Electronics. Copies shall  
not be reproduced or  
copied or used as the  
basis for the manufacture  
or sale of apparatus  
without permission.

