



PANDUIT PART NUMBER	DIMENSIONS - IN [mm]			TO BE USED WITH HTAP PART NUMBERS	*TO BE USED WITH CTAP PART NUMBERS
	L	W	H		
CVR6-1	2.00 [50.8]	1.20 [30.5]	1.26 [32.0]	N/A	CTAP4-8, CTAP4-6, CTAP4-4
CVR2-1	3.38 [85.9]	1.40 [35.6]	2.00 [50.8]	HTCT2-2	CTAP2-4, CTAP2-2, CTAP2/0-2
CVR250-1	3.38 [85.9]	1.55 [39.4]	2.05 [52.1]	HTCT250-250	CTAP2/0-2/0
CVR500-1	3.86 [98.0]	1.97 [50.0]	2.66 [67.6]	N/A	CTAP4/0-2, CTAP4/0-2/0, CTAP4/0-4/0
CVR1000-1	5.62 [142.7]	2.45 [62.2]	3.72 [94.5]	N/A	N/A

*NOTE: COVERS ARE NOT UL LISTED FOR USE WITH CTAP CONNECTORS

- NOTES:
1. MATERIAL: LOW DENSITY BLACK POLYPROPYLENE
 2. UL LISTED AND CSA CERTIFIED
 - WHEN USED WITH SPECIFIED HTAPS
 - MAXIMUM TEMPERATURE RATING: 90° C
 - VOLTAGE RATING OF COVER: 600V



								PANDUIT CORP. TINLEY PARK, ILLINOIS			
								CVR H-TAP COVERS CUSTOMER DRAWING			
04	1/11	JHNU	JHNU	ADDED NOTE TO SPECIFY PART IS NOT UL LISTED FOR USE WITH CTAP CONNECTORS	N41315BA-C41315	FLD	FLD	UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
03	12/10	JHNU	JHNU	REVISED AGENCY LOGO	N41315BA-C41315	FLD	FLD				
02	7/10	JHNU	JHNU	REMOVED HTCT8-8, HTCT6-6 FROM TABLE							
01	11/09	JHNU	JHNU	ADDED CVR6, CVR2, CVR500, & CVR1000 REVISED NOTES, ADDED TABLE				DRAWN BY	MAT'L: SEE NOTE 1 ABOVE	SCALE N/A	
00	8/09	JHNU	JHNU	DRAWING RELEASED				DATE		DRAWING NO / CAD FILE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D		C41315_04	DWG A SIZE