




MATERIAL NO.	ENGINEERING P/N	CARRIER STYLE
196060004	C-5293Z	METAL STRIP
196060005	C-5293	LOOSE PIECE
196060006	C-5293T	TAPE MOUNT




METAL CARRIER STRIP,
METAL STRIP PARTS ONLY



PARTS ON TAPE
SCALE: NONE



SECTION A-A



NOTES:

1. MATERIALS:
HOUSING: 94V-2 NYLON, YELLOW
TERMINAL: BRASS, .018/0.46 THICK REF., MATTE TIN PLATED
FERRULE: COPPER ALLOY, MATTE TIN PLATED
2. ACCEPTS TAB SIZE .250 x .032 (6.35 x 0.81).
3. MWD = MAXIMUM WIRE INSULATION DIAMETER.
4. PARTS ARE ROHS COMPLIANT.

RLS, FERRULE MAT'L EC NO: WNA2010-0610 DRWN:ETHRODAHL 2010/03/31 CHKD:JMACNEIL 2010/03/31 APPR:JMACNEIL 2010/04/12		DESCRIPTION REV	QUALITY SYMBOLS ▼=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 5:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY DATE ETHRODAHL 2010/03/31		TITLE FIQD FEMALE AVIKRIMP LOW PROFILE .250X.032 TAB, 12-10 AWG		
4 PLACES ± --- ± ---						CHECKED BY DATE JMACNEIL 2010/03/31		MOLEX MOLEX INCORPORATED		
3 PLACES ± --- ± ---						APPROVED BY DATE JMACNEIL 2010/04/09				
2 PLACES ± --- ± ---										
1 PLACE ± --- ± ---										
ANGULAR ±1/2°										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19606-003		SHEET NO. 1 OF 1
A						SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		