



VRLA Rechargeable Battery

BP4.5-12RT



FEATURES

- Absorbent Glass Mat technology for efficient gas recombination
- Maintenance free(no water topping-up required).
- No free acid(Non-spillable battery).
- Low self-discharge rate, lower than 3% capacity loss per month.
- Can be used in any orientation(excluding used inverted).

APPLICATION

- UPS
- Electronic Doorbells
- Toy-Cars
- Fans



SPECIFICATIONS

Nominal Voltage	12 V
Nominal Capacity	4.5Ah @ 20 hour rate F.V.(1.75V/cell)
Approx. Weight	1780g(3.92lbs.)
Terminals	+250 Faston/-187 Faston
Internal Resistance	≤42m Ω (Fully Charged)
Max. Discharge Current	67.5 A (5 sec.)
Maximum Charge Current	1.35 A
Operating Temperature Range	Charge : 0°C~40°C(32°F~104°F) Discharge : -20°C~50°C(-4°F~122°F) Storage : -20°C~40°C(-4°F~104°F)
Container Material	Standard: ABS(UL 94-HB) BP4.5-12RT Optional: Flame Retardant ABS(UL 94-V0) BP4.5-12RTFR



- IEC61056-1
- JIS C 8702-1
- GB/T 19639.1

DIMENSION(mm/inch)	OUTER DIMENSIONS	TERMINAL TYPE
Length 140±1.5 (5.51±0.06) Width 48±1.5 (1.89±0.06) Container Height 102±1.5 (4.02±0.06) Total Height 104±2.0 (4.09±0.08)		Terminal RT

Constant power discharge characteristics at 25 °C/77 °F Unit: W

Discharge Time F.V. (V/cell)	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	162.7	119.8	96.0	57.1	32.75	13.12	9.04	5.054	2.660
1.75V	188.3	129.8	100.4	59.3	33.73	13.38	9.18	5.130	2.700
1.70V	200.1	134.4	103.5	60.6	34.34	13.50	9.23	5.156	2.712
1.65V	209.1	137.6	105.9	61.5	34.75	13.59	9.26	5.171	2.724
1.60V	216.0	140.4	108.0	62.1	35.10	13.68	9.29	5.171	2.724

Constant current discharge characteristics at 25 °C/77 °F Unit: A

Discharge Time F.V. (V/cell)	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	14.66	10.54	8.35	4.84	2.75	1.09	0.754	0.421	0.222
1.75V	17.28	11.42	8.73	5.02	2.83	1.11	0.765	0.427	0.225
1.70V	18.36	11.83	9.00	5.14	2.89	1.12	0.769	0.430	0.226
1.65V	19.18	12.12	9.21	5.21	2.92	1.13	0.772	0.431	0.227
1.60V	19.82	12.36	9.39	5.26	2.95	1.14	0.774	0.431	0.227

All data and artworks shall be changed without prior notice, BB reserves the right to explain and update the information contained herein.