


1	2	3	4
Empfohlener Ausschnitt fuer Rastbefestigung (Gegensueber Bestueckungsseite) recommended cut-out for snap-in fixing (ledge opposite to snap-in direction)	Wanddicke wall thickness 0.8 bis/to 5.0	Ausschnittlaenge length of cut-out 27.2±0.1	Ausschnittbreite width of cut-out 12.2 ^{+0.2}



Aufschrift
Marking

155..
16(4)/250 ~ T100/55 T100
10(4)/250 ~ 5E4
5/100A 250V ~

05
16A 125-250V AC
1 HP 125V AC
2 HP 250V AC
R38

Schliesser 1-polig
Fuer Geraete der Klasse II geeignet

SPNO
suitable for appliances of class II

Herstellort/-jahr/-woche
nach DIN EN 60062
code of manufacture:
place/year/week
acc. to DIN EN 60062

fuer Form und Lage FOR SHAPE AND LOC.		☉ =	Allgemeintoleranzen UNTOLERANCED DIMENSIONS					Pause COPY	Blatt SHEET 01		TYP K	Zeichn./DRAWING NO. 15513202	Index e
			PROJEKTION	Abmasse und Nennmassbereiche Angaben in mm		Laenge LENGTH	Radial RADII						
0-6	± 0.2	± 0.2				0 10 20 30mm	Original Din A4	Masstab SCALE 1 : 1	GERAETESCHALTER appliance switch				
>6-15	± 0.4	±											
>15-30	± 0.4	±											
>30-70	±	±											
>70-120	±	±											
>120-200	±	±	ALL DIMENSIONS ARE IN MILLIMETRES			Ersatz fuer/REPLACEMENT OF Zg.gl.Nr.v.17.10.89							
d	51422	12.03.07	BRC						CAD: UG_NX6				
c	35129	26.02.03	WJ						gez./DRAWN BY 12.03.07 BRC gepr./CHECKED BY				
b	23635	09.11.95	RS						 MARQUARDT				
a	21323	05.05.92	MUT	e	69572							02.03.11	HHE
Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY		Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[1551.3202](#)