

test & measurement

products

skills

[download](#)

clamp-type test probes

- ▶ 0,64 mm system
- ▶ 2 mm system
- ▶ 2 mm Sicherheitssystem
- ▶ 4 mm system
- ▶ 4 mm sliding sleeve system
- ▶ 4 mm safety system

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

sets

miscellaneous

portrait

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

[terms and conditions](#)

[Home](#) ▶ [clamp-type test probes](#) ▶ [clamp-type test probe](#) ▶ [KLEPS 2600](#)

datasheet for KLEPS 2600
article number: 972306101



[View Full-Size Image](#)



product description:	order number: 972 306-101
description:	Safety clamp-type test probe with rotating grip jaws and flexible shaft. Wires and pins with up to a maximum diameter of 4mm can be clamped thanks to the special form of the grip jaws. 4mm diameter brass socket connection.
typ:	KLEPS 2600 rot/red
system:	4mm safety system
order number:	972 306-101
clamping range:	4 mm
clamping typ:	rotating grip jaws
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	4 A
Please consider derating curve!	
contact resistance:	50 mOhm
material	
contact material:	grip jaws: spring steel socket: brass
contact surface material:	grip jaws: tin
housing material:	PBT
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	
	