

OGA DIAGONAL: 34.19 [868.45]
VA DIAGONAL: 32.39 [822.76]
PA DIAGONAL: 30.53 [775.34]

TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-9121-205	98-0003-2693-8	FFC	8.00" [203.20]	AG500	23655
17-9121-226	98-0003-2962-7	USB R FW9	8.00" [203.20]	AG500	23655
17-9121-227	98-0003-2290-3	SER	8.00" [203.20]	AG500	23655
N/A	98-1100-0127-2	USB R	8.00" [203.20]	AG500	23655

(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE


(USB R FW9)
EXII-7769UC
98-0003-2815-7
USB CONTROLLER
SOLDER SIDE

(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE



ESD CLAMSHELL CASE
IS USED WITH ALL NOV,
USB AND SER
TERMINATIONS.

.147±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF



SECTION A-A
SCALE: NONE

.125
[3.18]
REF

17.065±.060
[433.45±1.52]
OUTER GLASS AREA

15.745
[399.92]
VIEWING AREA

14.857
[377.36]
PRECISION AREA

1.481
[37.62]

.660±.020
[16.76±0.51]

26.666
[677.31]
PRECISION AREA

28.308
[719.02]
VIEWING AREA

29.628±.060 [752.55±1.52]
OUTER GLASS AREA


NOTES:

1. WEIGHT OF GLASS IN GRAMS: 2485±10%
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

UNITS INCHES [MM]

TOLERANCES
UNLESS OTHERWISE SPECIFIED
.X ±
.XX ±.03 [.76]
.XXX ±.015 [.38]
ANGLES ±1°



DO NOT SCALE DRAWING

SCALE 1 = 1



3M TOUCH SYSTEMS
METHUEN, MA
USA

© COPYRIGHT
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN AH 8/07

H	REVISE PER CO 036120	2/13	SB
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING SCT32NN 32.39" W			
CAD FORMAT AUTOCAD		SHEET 1 OF 1	
SIZE E	DOCUMENT NO. TSD-34642	REV H	