


Self-aligning ball bearings, cylindrical and tapered bore, cylindrical bore, unsealed



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN	C_0	kN	r/min		kg	-
15	35	11	7,41	1,76	0,09	45000	28000	0,049	1202 ETN9



Calculation factors

- e 0,33
- Y_1 1,9
- Y_2 3
- Y_0 2