

Item		Description	
A. Construction - -			
A1. Conductor	A11	No. of conductor	25C
	A12	Material	Stranded ; tinned copper wire
	A13	AWG size & composition	24 AWG (7 strands / 0.20 mm)
	A14	Diameter	Nominal 0.6 mm
A2. Insulation	A21	Material	Semi-rigid Polyvinyl chloride (SR-PVC)RoHS
	A22	Nom. thickness	0.25 mm
	A23	Nom. diameter	1.1 mm
	A24	Rated Temperature	80 °C
	A25	Rated Voltage	300 V
A3. Shield	A31	Material & Manner	Overall Aluminum / polyester tape Wrapped , A1. side faced out.
	A32	Overlap	Min. 25 %
A4. Drain wire	A41	Material	Stranded ; tinned copper wire
	A42	AWG size & composition	24 AWG (7 strands / 0.20 mm)
	A43	Diameter	Nominal 0.60 mm
	A44	Note	The drain wire is laid in between Aluminum / polyester shield and braid.
A5. Braid	A51	Material	
	A52	Size & composition	
	A53	Coverage	
A6. Jacket	A61	Material	Polyvinyl chloride (PVC) RoHS
	A62	Nom. thickness	0.8 mm ↑
	A63	Overall diameter	9.0 + / - 0.15 mm
A7. Jacket printing			

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.		GOLDSUN NO.	
		2006377		SC25-500	
DRAWN: Ivan Wang		Description			Rev.
VERIFY PEOPLE: Jenny		CABLE, SHIELDED, 25 CONDUCTOR, GRAY, 24AWG,500FT, ROUND			1
		UNIT:	SCALE:	SHEET 1 OF 1	CAS No: ERN No:
		mm			

Item		Description	
A. Construction - -			
A1. Conductor	A11	No. of conductor	25C
	A12	Material	Stranded ; tinned copper wire
	A13	AWG size & composition	24 AWG (7 strands / 0.20 mm)
	A14	Diameter	Nominal 0.6 mm
A2. Insulation	A21	Material	Semi-rigid Polyvinyl chloride (SR-PVC)RoHS
	A22	Nom. thickness	0.25 mm
	A23	Nom. diameter	1.1 mm
	A24	Rated Temperature	80 °C
	A25	Rated Voltage	300 V
A3. Shield	A31	Material & Manner	Overall Aluminum / polyester tape Wrapped , A1. side faced out.
	A32	Overlap	Min. 25 %
A4. Drain wire	A41	Material	Stranded ; tinned copper wire
	A42	AWG size & composition	24 AWG (7 strands / 0.20 mm)
	A43	Diameter	Nominal 0.60 mm
	A44	Note	The drain wire is laid in between Aluminum / polyester shield and braid.
A5. Braid	A51	Material	
	A52	Size & composition	
	A53	Coverage	
A6. Jacket	A61	Material	Polyvinyl chloride (PVC) RoHS
	A62	Nom. thickness	0.8 mm ↑
	A63	Overall diameter	9.0 + / - 0.15 mm
A7. Jacket printing			

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO. 2006377		GOLDSUN NO. SC25-500	
DRAWN: Ivan Wang		Description CABLE, SHIELDED, 25 CONDUCTOR, GRAY, 24AWG,500FT, ROUND			Rev. 1
VERIFY PEOPLE: Jenny		UNIT: mm		SCALE:	SHEET 1 OF 1
				CAS No: ERN No:	