


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	TLY-13	NEMA 5-15P	1	white overmold
2	TLY-18L	C13, 90°	1	white overmold
3	30-00245	Wire, 3C, 18 AWG, UL SVT, 300V, 105°C, 6.3 mm, VW-1, PVC, white	1	



Revision	Date	Description	Notes		TENSILITY 20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com		
A	12/20/2012	Initial release					
			DIMENSIONS ARE IN MILLIMETERS	DESCRIPTION:	SIZE	Part number	
			TOLERANCES:	Ac cord, 1000 mm, U.S. NEMA 5-15P plug, TLY-13 to 90° C13, TLY-18L, 18 AWG, SVT, 30-00245, white	A	11-00036	
			X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm		SCALE:1:2	WEIGHT:	SHEET 1 OF 1