

CM SERIES

RELAY SOCKETS



CUSTOM CONNECTOR

DESCRIPTION	5, 8 and 11 Pin Square Base Sockets
ELECTRICAL RATING	• 300 Volts, 10 Amps • 150 Volts, 15 Amps
CONSTRUCTION	Contacts • Brass, Bright Tin Plated Molding • Break Resistant Thermoplastic Black Standard, White Available
AGENCY APPROVALS	• UL recognized, File No. E60008 • CSA certified, File No. LR29513 • CE




ORDERING CODE

PART NO.	DESCRIPTION	TERMINAL TYPE
CM05-SLD	SPDT, 5 Pin Square (Fig. 2)	Solder
CM05-LSLD	SPDT, 5 Pin Square (Fig. 2)	Long Solder
CM05-QDC	SPDT, 5 Pin Square (Fig. 1)	Quick Disconnect
CM08-SLD	DPDT, 8 Pin Square (Fig. 2)	Solder
CM08-LSLD	DPDT, 8 Pin Square (Fig. 2)	Long Solder
CM08-QDC	DPDT, 8 Pin Square (Fig. 1)	Quick Disconnect
CM11-SLD	3PDT, 11 Pin Square (Fig. 2)	Solder
CM11-LSLD	3PDT, 11 Pin Square (Fig. 2)	Long Solder
CM11-QDC	3PDT, 11 Pin Square (Fig. 1)	Quick Disconnect

ACCESSORIES

PART NO.	DESCRIPTION (Refer to the accessories pages 25-27)
HDB-5	Hold Down Spring

Fig. 1



PANEL CUT-OUT SIZE




Fig. 2

