



SPECIAL ELECTRONIC PLIERS EUROline-Conductive

CUTTING PLIERS

No.	Length		Finish	cutting capacity mm Ø			Weight g
	mm	inches		Medium hard wire	Hard wire	Plano- wire	

Carbide mini side cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
only for tough nickel and electrode wires

3-661-15	120	4 3/4	with side face very slim rounded head	1.2	1.0	0.6	60
3-663-15	120	4 3/4	with side face very slim pointed head with special flat cutting edge	0.6	0.5	-	60

Carbide oblique top cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
cutting plane 29° angular, for horizontal and vertical use,
only for tough nickel and electrode wires

3-667-15	115	4 1/2	without side face	0.6	0.5	0.3	65
----------	-----	-------	-------------------	-----	-----	-----	----

Glas fibre mini side cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
with special side face, **for cutting glass fibre only**, max. Ø 2.0 mm

3-665-15	120	4 3/4	very slim rounded head				60
----------	-----	-------	------------------------	--	--	--	----

ROUND, FLAT, SNIPE NOSE PLIERS

No.	Length		Finish	Weight g
	mm	inches		

Round nose pliers EUROline-Conductive

extremely slim

3-681-15	130	5 1/8	short plain jaws	60
----------	-----	-------	------------------	----

Flat nose pliers EUROline-Conductive

extremely slim

3-682-15	130	5 1/8	short plain jaws	60
3-688-15	130	5 1/8	short, ultra slim plain jaws	60

Snipe nose pliers EUROline-Conductive

extremely slim

3-683-15	130	5 1/8	short plain jaws	55
3-685-15	140	5 1/2	long plain jaws	65
3-686-15	140	5 1/2	long serrated jaws	65
3-687-15	130	5 1/8	short plain jaws, ultra slim pointed for precise handling of tiny components	60



3-661-15



3-663-15



3-667-15



3-665-15



3-681-15




3-682-15



3-688-15



3-683-15



3-685-15



3-687-15