

MNX ABS 175/60 HG



Order symbol: ABS 175/60 HG
Product nbr: 6081319
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074022974
El. number:
 Finland 3420561
 Denmark 8212023301
 Italy 7361110
 Sweden 2535763

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	L	W	H
mm:	180	180	60
inch:	7.1	7.1	2.4

Materials:

Material:	ABS
Gasket material:	TPE
Base colour:	RAL 7035
Cover colour:	RAL 7035
Cover screws material:	Polyamide
Cover screws colour:	Grey

Temperatures:

Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:

MIV 175	Mounting plate (Galvanized steel)
MIN 15	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 175/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

Rating:

Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 07

Certificates:

Fimko
Europe EN 50298: 1998
Gost R

