



UNIT: mm




CABLE BLACK PRINT
USB CABLE E189529 AWM 2725 28AWG/1PR AND
24AWG/2C 80°C 30V VW-1

PIN ASSIGNMENT:



Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 5 Ohm(max)
- 3. Insulation resistance: 5Mohm(min)
- 4. dielectric test: DC 300V



IPCS/PE BAG

⑧	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑦	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
⑥	TIE	1	WHITE L=100mm
⑤	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-65)
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-40P (MOULD NO: WM-40)
③	CABLE	1	BEIGE (IV-29#) USB1.1 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=2000 ± 10mm
②	CONN	1set	USB B MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
①	CONN	1set	USB A MALE SHELL: NICKEL, PIN G/F 3PCS TYPE INSULATOR COLOR: WHITE
NO.	NAME	QTY	SPECIFICATION

CNC Tech, LLC

Industrial Cable and Connector Technology

DRAWN	ZHONGHS	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1030-BE-00200
DECIDED		DATE	2012-02-15
VERSIONS/EDITION	A/0	PROJECTION	