


A B C D E F G H

| REV | DESCRIPTION | DATE           |
|-----|-------------|----------------|
| △   | RDK-96131   | 張馨尹 2008/01/03 |
| △   | RDK-98053   | 洗勝賢 2009/03/17 |



- NOTE :
1. MAXIMUM ELECTRIC CURRENT : 

|        |    |    |    |    |
|--------|----|----|----|----|
| A.W.G. | 22 | 20 | 18 | 16 |
| AMP.   | 3  | 4  | 7  | 10 |
  2. MAXIMUM ELECTRICAL RATING : 105°C 600 VOLTS MAX.
  3. INSULATION MATERIAL : VINYL
  4. INSULATION COLOR : RED
  5. TERMINAL MATERIAL : BRASS
  6. WIRE RANGE : 22-16 A.W.G. ( 0.5-1.5 mm<sup>2</sup> )
  7. NEMA TAB : 0.032 inch \* 0.187 inch ( 0.8 mm \* 4.75 mm )
  8. DOUBLE CRIMP : WITH COPPER SLEEVE ON BARREL
  9. TERMINAL SURFACE TREATMENT : TIN PLATED
  10. TERMINAL THICKNESS : 0.35 mm

| Tolerance Unless Otherwise Specified |              |
|--------------------------------------|--------------|
| 0 > 6 mm ± 0.20                      | ANGLE        |
| 6 > 18 mm ± 0.30                     | 0° > ° REF ± |
| 18 > 30 mm ± 0.40                    | ° > ° ±      |
| 30 > 75 mm ± 0.50                    | ° > ° ±      |

|          |                                                   |          |       |         |             |             |
|----------|---------------------------------------------------|----------|-------|---------|-------------|-------------|
| NAME     | VINYL-INSULATED DOUBLE CRIMP FEMALE DISCONNECTORS |          |       |         | UNIT        | mm          |
| PART NO. | FDD1-187(8)                                       | MATERIAL | ----- | APPROVE | [Signature] |             |
| NUMBER   | KA-951304-C                                       | SCALE    | SHEET | PAGE    | CHECKED     | [Signature] |
| DATE     | 2006/09/11                                        | 4/1      | 1-2   | 10F2    | DRAWN       | 謝婉如         |

**KST. K.S. TERMINALS INC.**

A B C D E F G H