


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	10/11/00



JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
6834	5.0	.060	.050	0.63	100,000	C-8
7134	5.0	.075	.090	1.13	25,000	C-8
7154	5.0	.115	.150	1.89	40,000	C-8

METRIC		DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION					
		TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE					
THIRD ANGLE PROJECTION		1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		T-1 STANDARD AXIAL LEAD LAMP					
DRAWN BY	APPR'D BY	DATE	SIZE	FSC# NO.		DRAWING NO.			
L. WENGSTROM	Q.C.	10/11/00	A	55335				AXIAL STANDARD T-1	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	NONE		RELEASED DATE	10/11/00	REVISION DATE	REV. NO.
									SHEET 1 OF 1