

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Circlip Pliers
Catalogue number	3710, 3711, 3712, 3713, 3716
Date	11/11/2008

Range Description

A range of professional quality Circlip pliers

Features

3710,3711, 3712 and 3713

- Forged and hardened for strength and performance
- Chequered handles for grip
- Leaf spring riveted to handle for a secure smooth action
- Conform to DIN standards

3716

- Features a push button adjustment which adapts the product for use on both inside and outside circlips
- Set includes one each inside and outside circlips in sizes 12, 14, 16, 18, 20 and 22mm



3710 Inside




3711 Outside



3712 Inside



3713 Outside



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3710 0	Circlip Plier Inside Straight 140mm	5013969491203	82032090	5
T3710 5	Circlip Plier Inside Straight 140mm	5013969491401	82032090	5
T3710 7	Circlip Plier Inside Straight 180mm	5013969491500	82032090	5
T3710 8	Circlip Plier Inside Straight 220mm	5013969491609	82032090	5
T3710 11	Circlip Plier Inside Straight 300mm	5013969491302	82032090	5
T3711 0	Circlip Plier Outside Straight 140mm	5013969491708	82032090	5
T3711 5	Circlip Plier Outside Straight 140mm	5013969491906	82032090	5
T3711 7	Circlip Plier Outside Straight 180mm	5013969492002	82032090	5
T3711 8	Circlip Plier Outside Straight 220mm	5013969492101	82032090	5
T3711 11	Circlip Plier Outside Straight 300mm	5013969491807	82032090	5
T3712 5	Circlip Plier Inside Bent 140mm	5013969492408	82032090	5
T3712 7	Circlip Plier Inside Bent 180mm	5013969492507	82032090	5
T3712 8	Circlip Plier Inside Bent 220mm	5013969492602	82032090	5
T3713 0	Circlip Plier Outside Bent 140mm	5013969492705	82032090	5
T3713 5	Circlip Plier Outside Bent 140mm	5013969492903	82032090	5
T3713 7	Circlip Plier Outside Bent 180mm	5013969493009	82032090	5
T3713 8	Circlip Plier Outside Bent 220mm	5013969493108	82032090	5
T3716	Circlip Plier Set Adjustable Inside/Outside	5013969027556	82032090	3

Technical product information	Sizes of Circlips by item		
	Item	Circlip Dia	DIN Size code
	T3710 0	8-13mm	J0
	T3710 5	12-25mm	J1
	T3710 7	19-60mm	J2
	T3710 8	40-100mm	J3
	T3710 11	85-140mm	J4
	T3711 0	3-10mm	A0

	T3711 5	10-25mm	A1
	T3711 7	19-60mm	A2
	T3711 8	40-100mm	A3
	T3711 11	85-140mm	A4
	T3712 5	12-25mm	J11
	T3712 7	19-60mm	J21
	T3712 8	40-100mm	J31
	T3713 0	3-10mm	A01
	T3713 5	10-25mm	A11
	T3713 7	19-60mm	A21
	T3713 8	40-100mm	A31
	Standards compliance	3710 to DIN 5256C 3711 to DIN 5254A 3712 to DIN 5256D 3713 to DIN 5254B	
User health and safety information	Users and bystanders are advised to wear safety goggles		
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations		
Material safety data	None applicable		
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through in appropriate use is not covered		
Country of origin	3710, 3711, 3712 & 3713 – Germany 3716 – Taiwan		

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3710 0	42	10	142	87	48	25	204	94
T3710 5	42	10	142	87	48	25	204	94
T3710 7	45	14	175	140	48	25	225	148
T3710 8	45	14	225	223	48	25	255	241
T3710 11	52	15	320	421	61	25	330	435
T3711 0	74	10	140	95	50	25	215	102
T3711 5	74	10	140	95	50	25	215	102
T3711 7	91	14	175	155	48	25	225	163
T3711 8	104	13	222	226	48	25	270	235
T3711 11	155	16	320	450	61	25	360	464

T3712 5	42	10	132	87	48	25	204	94
T3712 7	45	14	175	140	48	25	225	148
T3712 8	44	26	210	223	48	25	255	241
T3713 0	76	17	130	95	50	25	215	102
T3713 5	76	17	130	95	50	25	215	102
T3713 7	91	21	156	155	48	25	225	163
T3713 8	104	27	224	226	48	25	270	235
T3716	100	28	160	130	105	40	210	284

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3710 0	80	250	63	538		
T3710 5	80	250	63	538		
T3710 7	80	250	63	808		
T3710 8	90	290	63	1281		
T3710 11	130	340	57	2229		
T3711 0	80	250	63	581		
T3711 5	80	250	63	585		
T3711 7	80	250	63	883		
T3711 8	90	290	63	1254		
T3711 11	130	340	57	2396		
T3712 5	80	250	63	538		
T3712 7	80	250	63	808		
T3712 8	90	290	63	1281		
T3713 0	80	250	63	581		
T3713 5	80	250	63	585		
T3713 7	80	250	63	883		
T3713 8	90	290	63	1254		
T3716	135	230	115	1000		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use

T3710 0	8	cliphanger					68	Box
T3710 5	8	cliphanger					68	box
T3710 7	8	cliphanger					68	box
T3710 8	8	cliphanger					76	box
T3710 11	14	cliphanger					94	box
T3711 0	8	cliphanger					68	box
T3711 5	8	cliphanger					68	box
T3711 7	8	Clip hanger					68	Box
T3711 8	8	cliphanger					76	box
T3711 11	14	cliphanger					94	box
T3712 5	8	cliphanger					68	box
T3712 7	8	cliphanger					68	box
T3712 8	8	cliphanger					76	box
T3713 0	8	cliphanger					68	box
T3713 5	8	cliphanger					68	box
T3713 7	8	cliphanger					68	box
T3713 8	8	cliphanger					76	box
T3716	2	Wrap					140	Box