

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD


P

REVISED PER ECO-11-005140


02APR2011

RK



HMR



断面 A-A



断面 B-B




1. 適用電線; AVSS, CAVS, CAVUS, AVSSH-f 0.3~0.5mm²
2. アプリケータ送りピッチ; 7.5mm

1. APPLICABLE WIRE RANGE;
AVSS, CAVS, CAVUS, AVSSH-f 0.3~0.5mm²
2. APPLICATOR FEED; 7.5mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: mm



MATERIAL
材料 COPPER Alloy

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差 ±0.3
0-PLC ±
1-PLC ±0.5
2-PLC ±0.13
3-PLC ±0.013
4-PLC ±0.000
ANGLES ±3'00"

FINISH
仕上 SEE TABLE

DWN S. FURUYA 19-JUN-03

CHK T. KOHNO 19-JUN-03

APVD K. SHIMIZU 19-JUN-03

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

114-5340

WEIGHT 0.2g

CUSTOMER DRAWING

WIRE RANGE
包合電線断面積 0.37~0.56mm²

INSULATION DIA
被覆外径 Ø1.1~1.7



TE Connectivity

NAME

名称

025 TH TAB CONTACT

SIZE

寸法

CAGE CODE

番号

DRAWING NO

番号

1674742

RESTRICTED TO

制限範囲

SCALE

尺度

SHEET

枚数

OF

1

REV

P