


REV. 1 5/12/93 JAW



THIS ITEM IS AVAILABLE WITH GROUP 'A' TESTING FOR RELIABILITY LEVEL 'L' & 'M' IN ACCORDANCE WITH TABLE V MIL-R-39016D. FOR THIS OPTION ADD 'L' OR 'M' TO PART NUMBER (i.e. CAW-1C-6BL)

COIL:

RESISTANCE 40 OHMS $\pm$ 10%
 NOMINAL VOLTAGE 6.0 VDC
 MUST OPERATE 3.5 VDC
 MUST RELEASE .45 VDC


ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 5 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: DIELECTRIC 1000 VRMS EXCEPT 500
VRMS ACROSS OPEN CONTACTS.

CUSTOMER DATA SHEET

BLUE BEAD



CONTACT RATING: 10 AMP/28 VDC
RESISTIVE 50,000 OPERATIONS

DR. R.B. 5/12/93 CK. JAW 5-12-93

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.
 CUST. NO. _____

TYPE 'C' RELAY

CAW-1C-6B