

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015995162

Status:

Obsolete

Description:

2.54mm (.100") Pitch MX-50™ Slimline Ribbon Cable Connector, Feed-To Version
Preloaded Upper Housing, 16 Circuits

Documents:

Drawing (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Ribbon Cable / Wire Trap Connectors
Series	70121
Comments	Feed-To Left-Hand Cable Stop
Component Type	Housing
Glow-Wire Compliant	No
Product Name	MX-50™

Physical

Circuits (Loaded)	16
Entry Angle	90° Angle
Flammability	94V-0
Lock to Mating Part	Yes
Number of Rows	2
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.54mm (.100")
Polarized to Mating Part	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	1.14mm (.045") max.
Wire Size AWG	26, 28
Wire/Cable Type	Ribbon Cable

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Material Info

Old Part Number	70121-9055
-----------------	------------

EU RoHS

ELV and RoHS
Compliant

REACH SVHC
Not Reviewed

Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

70121Series

Mates With

8624 , 70203

Use With

6800 Tinned Molex cable (28 AWG), 40158 Topcoat Molex Cable (28 AWG), 8863 Tinned Molex Cable (26 AWG)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION