


# Data sheet

---



**Application:** A mild steel IP66 industrial wall box suitable for housing electronic and electrical equipment in demanding environments, where the area is prone to frequent hosing or generally wet conditions.

**Supply Includes:** Enclosure and door mounting plate, double locking system, gland plate, sealing gasket and fixing accessories.

**Standard Configuration:** Paint finish epoxy polyester powder coating textured finish


**Color:** RAL7032

**Protection degree:** IP66

**Against mechanical impacts:** IK10

**Thickness:** enclosure & door 1.2mm or 1.5mm sheet steel

**Mounting plate:** zinc-coated steel 1.5mm or 2.0mm



| Stock no. | Description | Height (mm) | Width (mm) | Depth (mm) | Body & door thickness (mm) | Mounting plate thickness (mm) |
|-----------|-------------|-------------|------------|------------|----------------------------|-------------------------------|
| 775-5817  | Double lock | 600         | 400        | 200        | 1.2                        | 1.5                           |
| 775-5338  | Double lock | 600         | 400        | 210        | 1.2                        | 1.5                           |
| 775-5347  | Double lock | 600         | 400        | 300        | 1.2                        | 1.5                           |
| 775-5811  | Double lock | 600         | 500        | 200        | 1.2                        | 1.5                           |
| 775-5820  | Double lock | 600         | 600        | 200        | 1.2                        | 1.5                           |
| 775-5340  | Double lock | 600         | 600        | 210        | 1.2                        | 1.5                           |
| 775-5344  | Double lock | 600         | 600        | 300        | 1.2                        | 1.5                           |
| 775-5353  | Double lock | 600         | 600        | 400        | 1.2                        | 1.5                           |
| 775-5823  | Double lock | 700         | 500        | 200        | 1.2                        | 1.5                           |
| 775-5356  | Double lock | 700         | 500        | 260        | 1.2                        | 1.5                           |
| 775-5827  | Double lock | 800         | 600        | 200        | 1.5                        | 2                             |
| 775-5350  | Double lock | 800         | 600        | 210        | 1.5                        | 2                             |
| 775-5362  | Double lock | 800         | 600        | 300        | 1.5                        | 2                             |
| 775-5369  | Double lock | 800         | 600        | 260        | 1.5                        | 2                             |